

# YA38TC58FXB45

by Burndy  
Catalog ID: YA38TC58FXB45

Prop 65 Notice

UL Listed 90° C, 600 Volts to 35kV.



## Product Details

### General

Color Code	Pink
Connector Type	Terminal
Die Index	L99
Feature - Barrel Style	Belled
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated
UPC	781810238585
UPC 12 Digit	7818102385855

### Dimensions

Dimension - B Length fraction	3-1/16 in
Dimension - B Length inch	3.08 in
Dimension - Bolt Hole Size inch	0.66 in
Dimension - Bolt Size fraction	5/8
Dimension - Height inch	3.78 in
Dimension - Hole Size inch	0.69 in
Dimension - Hole Size mm	18 mm
Dimension - L Length Overall mm	121 mm
Dimension - Length Overall inch	4.77 in
Dimension - N inch	0.66 in
Dimension - Outside Diameter inch	1.25 in
Dimension - Pad Width inch	1.84 in
Dimension - Strip Length inch	3-3/16
Dimension - Z inch	0.53 in
Physical Attribute - Tongue Angle	45 Degree

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper DLO Size	535.3 (1325/#24)
Conductor - Copper DLO Size Range	535.3 (1325/#24)
Conductor - Copper Flex G Size	535.3
Conductor - Copper Flex G Size Range	535.3
Conductor - Copper Flex H Size	535.3
Conductor - Copper Flex H Size Range	535.3
Conductor - Copper Flex I Size	535.3
Conductor - Copper Flex I Size Range	535.3
Conductor - Copper Flex K Size	535.3
Conductor - Copper Flex K Size Range	535.3
Conductor - Copper Flex M Size	535.3
Conductor - Material	Copper

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity	6
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)