

# YA392LH95TN

by Burndy  
Catalog ID: YA392LH95TN

Cu Battery Terminal, 2 Holes w/o Inspection Window, CLASS K:500 kcmil Flex, 5054/30 STR, 1/2" stud, Standard, Compression



## Product Details

### General

Connector Type	Terminal
Die Index	1029
Feature - Barrel Style	Shrouded
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Shrouded Barrel, Tin Plated
UPC	781810026007
UPC 12 Digit	7818100260077

### Dimensions

Dimension - B Length fraction	1-7/8 in
Dimension - B Length inch	1.88 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	177 mm
Dimension - Length BB inch	1.00 in
Dimension - Length Overall inch	6.97 in
Dimension - N inch	0.53 in
Dimension - Outside Diameter inch	1.30 in
Dimension - Pad Width inch	1.91 in
Dimension - Z inch	2.32 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

## Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Flex G Size	500 kcmil
Conductor - Copper Flex G Size Range	500 kcmil
Conductor - Copper Flex H Size	500 kcmil
Conductor - Copper Flex H Size Range	500 kcmil
Conductor - Copper Flex I Size	500 kcmil
Conductor - Copper Flex I Size Range	500 kcmil
Conductor - Copper Flex K Size	500 kcmil
Conductor - Copper Flex K Size Range	500 kcmil
Conductor - Copper Flex M Size	500 kcmil
Conductor - Copper Flex M Size Range	500 kcmil
Conductor - Material	Copper

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	25
-----------------------	----

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)