



YA392TC38

by Burndy
Catalog ID: YA392TC38

Prop 65 Notice

Copper Compression Lug, 2 Hole w/o Inspection Window, 750 kcmil, 3/8" Stud, 1" Stud Hole Spacing, Long Barrel, Tin Plated

Product Details

General

Color Code	Black
Connector Type	Terminal
Die Index	24
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated
UPC	781810821244
UPC 12 Digit	7818108212444

Dimensions

Dimension - B Length fraction	2-7/8 in
Dimension - B Length inch	2.88 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - Hole Size inch	0.40 in
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	149 mm
Dimension - Length Overall inch	5.87 in
Dimension - N inch	0.50 in
Dimension - Outside Diameter inch	1.30 in
Dimension - Pad Width inch	1.63 in
Dimension - Strip Length inch	2-15/16
Dimension - Stud Size inch	3/8
Dimension - Z inch	0.53 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Size	750 kcmil
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)