

YA39A34

by Burndy
Catalog ID: YA39A34

Prop 65 Notice

UNINSULATED ALUMINUM COMPRESSION TERMINAL, 1-HOLE
DESIGNUL Listed 90° C600 Volts to 35 KV.



Product Details

General

Color Code	Yellow
Connector Type	Terminal
Die Index	936
Feature - Barrel Type	Standard
Material	Aluminum
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
UPC	781810569047
UPC 12 Digit	7818105690477

Dimensions

Dimension - D inch	2.19 in
Dimension - L Length Overall mm	157 mm
Dimension - Length Overall inch	6.17 in
Dimension - N inch	1.00 in
Dimension - Pad Width inch	2.05 in
Dimension - Strip Length inch	2-7/8
Dimension - Stud Size inch	3/4
Dimension - Z inch	1.19 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Size	700 - 750 Kcmil
-----------------------------	-----------------

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)