

YA39A5DT

by Burndy
Catalog ID: YA39A5DT

Prop 65 Notice

Uninsul Al Comp Terminal, Sealed, 2 Hole NEMA, 700-750 kcmil(Al/Cu), 900 kcmil Compt AL, 600 V-35 kV, 1/2" Stud, 1.75" Spacing, Closed bbl, Yellow, 936 Index



Product Details

General

Color Code	Yellow
Connector Type	Terminal
Die Index	936
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Aluminum
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
UPC	781810268407
UPC 12 Digit	7818102684077

Dimensions

Dimension - B Length fraction	2-7/16 in
Dimension - B Length inch	2.46 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - D inch	3.15 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	180 mm
Dimension - Length Overall inch	7.07 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	1.46 in
Dimension - Pad Width inch	1.62 in
Dimension - Thread Size	1/2
Dimension - Z inch	0.77 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - AL Str Size	700 kcmil;715 kcmil;750 kcmil
Conductor - AL Str Size Range	700 kcmil-750 kcmil
Conductor - Copper Str Size	700 kcmil;750 kcmil
Conductor - Copper Str Size Range	700 kcmil-750 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	3
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)