



YA39L2NT3890

by Burndy
Catalog ID: YA39L2NT3890

Copper Compression Lug, 2 Holes w/ Inspection Window, 750 kcmil, 3/8" Stud, 24 index, Black, Tin Plated, 90 Degree Bend

Product Details

General

Color Code	Black
Connector Type	Terminal
Die Index	24
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
UPC	781810035689

Dimensions

Dimension - B Length fraction	1-7/16 in
Dimension - B Length inch	1.42 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - D inch	2.06 in
Dimension - L Length Overall mm	75 mm
Dimension - Length Overall inch	2.97 in
Dimension - N inch	0.50 in
Dimension - Outside Diameter inch	1.30 in
Dimension - Pad Width inch	1.63 in
Dimension - Strip Length inch	1-1/2
Dimension - Stud Size inch	3/8
Dimension - Z inch	0.56 in
Physical Attribute - Tongue Angle	90 Degree

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Size	750 kcmil
Conductor - Copper Str Size Range	750 kcmil

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	6
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)