

## YA39L2NT38

by Burndy  
Catalog ID: YA39L2NT38

Prop 65 Notice

Code Conductor Standard Barrel Narrow, 750 kcmil, 3/8 in, 4.34 in L.

Features: UL Listed 90 DEG C, 600 V - 35 KV, 45 DEG And 90 DEG Angles Are Available, Die Index: 24, Finish: Electro-Tin Plated, Wire Strip Length: 1-15/16 IN, Tongue Angle: Straight, Temperature Rating: 90 DEG C, Color Code: Black, Tools, Die Set Catalog Number, And (number Of Crimps): Hydraulic: Y35, Y39, Y750, PAT750 Tool, U39RT Die, (2), Y46 Tool, U39RT Die With PUADP-1 Adapter, (2), Conductor Type: Commercial Stranded Copper, Dieless Tools (number Of Crimps): Y644HS, Y81KFT, Y81KFTMBH, PAT81KFT-18V Tool, (1)



## Product Details

### General

Application	For Code Conductor
Color Code	Black
Connector Type	Terminal
Die Index	24
Feature - Barrel Style	<ul style="list-style-type: none"> <li>Chamfered</li> <li>Skived</li> </ul>
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	YA-L-2NT, Code Conductor Standard Barrel Narrow Tongue
UPC	781810503638

### Dimensions

Dimension - B Length fraction	1-7/16 in
Dimension - B Length inch	1.42 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - D inch	2.06 in
Dimension - L Length Overall mm	110 mm
Dimension - Length Overall inch	4.34 in
Dimension - N inch	0.50 in
Dimension - Outside Diameter inch	1.30 in
Dimension - Pad Width inch	1.63 in

Dimension - Strip Length inch	1-1/2
Dimension - Stud Size inch	3/8
Dimension - Z inch	0.56 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Size	750 kcmil
Conductor - Copper Str Size Range	750 kcmil

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
 47 East Industrial Park Drive  
 Manchester, New Hampshire 03109

**Customer Service Hours:**  
 8 AM - 8 PM Eastern Monday-Friday  
 Emergency Service 24-hours/365 Days  
 Phone: 1-800-346-4175  
 1-603-647-5299 (International)