

YA39L2TC3845

by Burndy
Catalog ID: YA39L2TC3845

Prop 65 Notice

Copper Compression Terminal, 2 Hole, Tin-Electro Plated, 750 Kcmil



Product Details

General

| | |
|--------------------------------------|---|
| Color Code | Black |
| Connector Type | Terminal |
| Die Index | 24 |
| Feature - Barrel Style | <ul style="list-style-type: none"> • Chamfered • Skived |
| Feature - Barrel Type | Standard |
| Material | Copper |
| Physical Attribute - Number of Holes | 2 |
| Physical Attribute - Tongue Type | Standard |
| Plated | Y |
| Plating Type | Tin - Electro Plated |
| Trade Name | HYLUG™ |
| Type | Standard Barrel, Tin Plated |
| UPC | 781810021194 |
| UPC 12 Digit | 7818100211944 |

Dimensions

| | |
|-----------------------------------|-----------|
| Dimension - B Length fraction | 1-7/16 in |
| Dimension - B Length inch | 1.42 in |
| Dimension - Bolt Hole Size inch | 0.39 in |
| Dimension - Bolt Size fraction | 3/8 |
| Dimension - Height inch | 2.65 in |
| Dimension - Hole Size inch | 0.40 in |
| Dimension - Hole Size mm | 10 mm |
| Dimension - L Length Overall mm | 109 mm |
| Dimension - Length Overall inch | 4.31 in |
| Dimension - N inch | 0.50 in |
| Dimension - Outside Diameter inch | 1.30 in |
| Dimension - Pad Width inch | 1.91 in |
| Dimension - Strip Length inch | 1-15/16 |
| Dimension - Stud Size inch | 3/8 |

| | |
|-----------------------------------|-----------|
| Dimension - Z inch | 0.52 in |
| Physical Attribute - Tongue Angle | 45 Degree |

Electrical Ratings

| | |
|--------------------------|-------|
| Rating - KVA | 35 kV |
| Rating - Minimum Voltage | 600 |
| Voltage - Maximum | 35000 |

Conductor Related

| | |
|-----------------------------------|-----------|
| Conductor - Copper DLO Size Range | N/A |
| Conductor - Copper Str Size | 750 kcmil |
| Conductor - Material | Copper |

Certifications and Compliance

| | |
|------------------------------------|--------------|
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Industry Standard(s) | UL 486A-486B |
| Standards - Industry Standards Met | UL 486A-486B |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|----|
| Minimum Pack Quantity | 25 |
|-----------------------|----|

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)