

# YA39L945

by Burndy  
Catalog ID: YA39L945

Copper Compression Lug, Single Hole w/ Inspection Window, 750 kcmil, 1-1/4" Stud, 24 index, Black, Tin Plated, 45 Degree Bend



## Product Details

### General

Color Code	Black
Connector Type	Terminal
Die Index	24
Feature - Barrel Style	<ul style="list-style-type: none"> <li>• Chamfered</li> <li>• Skived</li> </ul>
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810021323

### Dimensions

Dimension - B Length fraction	1-7/16 in
Dimension - B Length inch	1.42 in
Dimension - D inch	2.52 in
Dimension - Height inch	2.65 in
Dimension - Hole Size mm	33 mm
Dimension - L Length Overall mm	122 mm
Dimension - Length Overall inch	4.80 in
Dimension - N inch	1.25 in
Dimension - Outside Diameter inch	1.30 in
Dimension - Pad Width inch	1.91 in
Dimension - Strip Length inch	1-15/16
Dimension - Stud Size inch	1-1/4 in
Dimension - Z inch	1.27 in
Physical Attribute - Tongue Angle	45 Degree

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Size	750 kcmil
Conductor - Copper Str Size Range	750 kcmil
Conductor - Material	Copper

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity	6
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)