

YA39LNT12

by Burndy
Catalog ID: YA39LNT12

Prop 65 Notice

1 Hole HYLUG Uninsulated Cu Compression Terminal, Narrow Tongue,
750 kcmil, 600 V - 35 KV, 1/2" stud, Standard Barrel, Black



Product Details

General

Color Code	Black
Connector Type	Terminal
Die Index	24
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
UPC	781810261699

Dimensions

Dimension - B Length fraction	1-7/16 in
Dimension - B Length inch	1.42 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - D inch	1.70 in
Dimension - L Length Overall mm	108 mm
Dimension - Length Overall inch	4.24 in
Dimension - N inch	0.53 in
Dimension - Outside Diameter inch	1.30 in
Dimension - Pad Width inch	1.63 in
Dimension - Strip Length inch	1-15/16
Dimension - Stud Size inch	1/2
Dimension - Z inch	1.07 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600

Voltage - Maximum	35000
-------------------	-------

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Size	750 kcmil
Conductor - Copper Str Size Range	750 kcmil

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	25
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)