

# YA3C2NU

by Burndy  
Catalog ID: YA3C2NU

Prop 65 Notice

Cu Compression Terminal, Blank Tongue, #3 AWG-#2 SOL, 4.62 IN L



## Product Details

### General

Color Code	White
Connector Type	Terminal
Die Index	9
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	0
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated
UPC	781810138106

### Dimensions

Dimension - B Length fraction	1-1/4 in
Dimension - B Length inch	1.25 in
Dimension - L Length Overall mm	117 mm
Dimension - Length Overall inch	4.62 in
Dimension - Outside Diameter inch	0.38 in
Dimension - Pad Width inch	0.83 in
Dimension - Strip Length inch	1-5/16
Dimension - Stud Size inch	1/4
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper Solid Size	2 AWG
Conductor - Copper Str Navy Size	50 (19) Navy

Conductor - Copper Str Size	3 AWG
Conductor - Material	Copper

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)