



YA3C90

by Burndy
Catalog ID: YA3C90

Prop 65 Notice

Copper HYLUG™, 0.98 in in long

Product Details

General

| | |
|--------------------------------------|-------------------------|
| Color Code | White |
| Connector Type | Terminal |
| Die Index | 9 |
| Feature - Barrel Style | Chamfered |
| Feature - Barrel Type | Long |
| Material | Copper |
| Physical Attribute - Number of Holes | 1 |
| Plated | Y |
| Plating Type | Tin |
| Trade Name | HYLUG™ |
| Type | Long Barrel, Tin Plated |
| UPC | 781810316054 |

Dimensions

| | |
|-----------------------------------|-----------|
| Dimension - B Length fraction | 1-1/4 in |
| Dimension - B Length inch | 1.25 in |
| Dimension - Bolt Hole Size inch | 0.33 in |
| Dimension - Height inch | 1.73 in |
| Dimension - Hole Size inch | 0.33 in |
| Dimension - Hole Size mm | 8 mm |
| Dimension - L Length Overall mm | 25 mm |
| Dimension - Length Overall inch | 0.98 in |
| Dimension - N inch | 0.34 in |
| Dimension - Outside Diameter inch | 0.38 in |
| Dimension - Pad Width inch | 0.55 in |
| Dimension - Strip Length inch | 1-5/16 |
| Dimension - Z inch | 0.36 in |
| Physical Attribute - Tongue Angle | 90 Degree |

Electrical Ratings

| | |
|--------------|-------|
| Rating - KVA | 35 kV |
|--------------|-------|

| | |
|--------------------------|-------|
| Rating - Minimum Voltage | 600 |
| Voltage - Maximum | 35000 |

Conductor Related

| | |
|----------------------------------|--------------|
| Conductor - Copper Str Navy Size | 50 (19) Navy |
| Conductor - Copper Str Size | 3 AWG |
| Conductor - Material | Copper |

Certifications and Compliance

| | |
|------------------------------------|--------------|
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Industry Standard(s) | UL 486A-486B |
| Standards - Industry Standards Met | UL 486A-486B |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|----|
| Minimum Pack Quantity | 25 |
|-----------------------|----|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)