

YA3CLD

by Burndy
Catalog ID: YA3CLD

COPPER COMPRESSION TERMINAL 2.30 inches long, Lead Plated



Product Details

General

Color Code	White
Connector Type	Terminal
Die Index	9
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Lead plated
Temperature Rating	194
Trade Name	HYLUG™
Type	Long Barrel, Lead Plated
UPC	781810020326
UPC 12 Digit	7818100203266

Dimensions

Dimension - B Length inch	1.25 in
Dimension - Bolt Hole Size inch	0.33 in
Dimension - D inch	0.70 in
Dimension - Hole Size inch	0.33 in
Dimension - Hole Size mm	8 mm
Dimension - L Length Overall mm	58 mm
Dimension - Length Overall inch	2.30 in
Dimension - N inch	0.34 in
Dimension - Outside Diameter inch	0.38 in
Dimension - Pad Width inch	0.55 in
Dimension - Strip Length inch	1-5/16
Dimension - Z inch	0.36 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Solid Size	2 AWG
Conductor - Copper Solid Size Range	2 AWG
Conductor - Copper Str Navy Size	50 (19) Navy
Conductor - Copper Str Navy Size Range	50 (19) Navy
Conductor - Copper Str Size	3 AWG
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	NC
UL Listed	Yes

Logistics

Carton Quantity	100
Minimum Pack Quantity	200

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)