

YA3CN45

by Burndy
Catalog ID: YA3CN45

COPPER COMPRESSION TERMINAL 2.68 inches long, Electro Tin Plated



Product Details

General

Color Code	White
Connector Type	Terminal
Die Index	9
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Electro Tin Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated
UPC	781810316252
UPC 12 Digit	7818103162522

Dimensions

Dimension - B Length inch	1.25 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - D inch	1.27 in
Dimension - Height inch	1.41 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	68 mm
Dimension - Length Overall inch	2.68 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	0.38 in
Dimension - Pad Width inch	0.83 in
Dimension - Strip Length inch	1-5/16
Dimension - Z inch	0.64 in
Physical Attribute - Tongue Angle	45 Degree

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Navy Size	50 (19) Navy
Conductor - Copper Str Navy Size Range	50 (19) Navy
Conductor - Copper Str Size	3 AWG
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	10
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)