

YA3CNB

by Burndy
Catalog ID: YA3CNB

Prop 65 Notice

Uninsulated Cu Compression Belled Terminal, 1-Nema Hole W/O
InspWindow, #3 AWG, 1/2" Stud, Long Barrel



Product Details

General

Color Code	White
Connector Type	Terminal
Feature - Barrel Style	Belled
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
UPC	781810126752
UPC 12 Digit	7818101267522

Dimensions

Dimension - B Length fraction	1-3/16 in
Dimension - B Length inch	1.18 in
Dimension - D inch	1.27 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - Inside Diameter inch	0.28 in
Dimension - L Length Overall mm	73 mm
Dimension - Length Overall inch	2.88 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	0.38 in
Dimension - Pad Width inch	0.83 in
Dimension - Z inch	0.64 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600

Voltage - Maximum	35000
-------------------	-------

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Navy Size	50 (19) Navy
Conductor - Copper Str Navy Size Range	50 (19) Navy
Conductor - Copper Str Size	3 AWG
Conductor - Copper Str Size Range	3 AWG
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	25
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)