

YA40LNTM20FX

by Burndy
Catalog ID: YA40LNTM20FX

Cu Compression Terminal, Narrow Tongue, 1 Hole W/InspWindow, 646.4 (1600/#24)DLO (650 kcmil Flex), 20 mm Bolt



Product Details

General

Color Code	Black
Connector Type	Terminal
Die Index	24
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin
Temperature Rating	194
Trade Name	HYLUG™
UPC	781810269534
UPC 12 Digit	7818102695344

Dimensions

Dimension - B Length fraction	1-7/16 in
Dimension - B Length inch	1.42 in
Dimension - Hole Size inch	0.85 in
Dimension - L Length Overall mm	98 mm
Dimension - Length Overall inch	3.85 in
Dimension - N inch	0.75 in
Dimension - Outside Diameter inch	1.35 in
Dimension - Pad Width inch	1.71 in
Dimension - Strip Length inch	1-5/16
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	646 (1600/#24)
Conductor - Copper DLO Size Range	646 (1600/#24)
Conductor - Copper Flex G Size	650
Conductor - Copper Flex G Size Range	650
Conductor - Copper Flex H Size	650
Conductor - Copper Flex H Size Range	650
Conductor - Copper Flex I Size	650
Conductor - Copper Flex I Size Range	650
Conductor - Copper Flex K Size	650
Conductor - Copper Flex K Size Range	650
Conductor - Copper Flex M Size	650

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	12
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)