



YA40LTC58FX

by Burndy
Catalog ID: YA40LTC58FX

Prop 65 Notice

Copper Tubing Terminal, 1 Hole W/insp window, 646.4 (1600/#24) DLO,
650 kcmil/Flex, 3.68 IN L, 24 Index

Product Details

General

Color Code	Black
Connector Type	Terminal
Die Index	24
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810033302
UPC 12 Digit	7818100333022

Dimensions

Dimension - B Length fraction	1-7/16 in
Dimension - B Length inch	1.42 in
Dimension - Bolt Hole Size inch	0.66 in
Dimension - Bolt Size fraction	5/8
Dimension - Hole Size inch	0.69 in
Dimension - Hole Size mm	18 mm
Dimension - L Length Overall mm	93 mm
Dimension - Length Overall inch	3.68 in
Dimension - N inch	0.66 in
Dimension - Outside Diameter inch	1.35 in
Dimension - Pad Width inch	1.98 in
Dimension - Strip Length inch	1-5/16
Dimension - Stud Size inch	5/8
Dimension - Thread Size	5/8 in

Dimension - Z inch	0.67 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	646 Kcmil
Conductor - Copper Flex G Size	650 Kcmil
Conductor - Copper Flex H Size	650 Kcmil
Conductor - Copper Flex I Size	650 Kcmil
Conductor - Copper Flex K Size	650 Kcmil
Conductor - Copper Flex M Size	650 Kcmil
Conductor - Copper Str Size	400 mm2
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	20
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)