

## YA412L

by Burndy  
Catalog ID: YA412L

Copper Compression Lug, 2 Holes w/ Inspection Window, 800 kcmil, 3/8" Stud, Short Barrel, 26 index, Gold, Tin Plated



## Product Details

### General

Color Code	Gold
Connector Type	Terminal
Die Index	26
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810367407

### Dimensions

Dimension - B Length fraction	1-7/8 in
Dimension - B Length inch	1.88 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - D inch	2.15 in
Dimension - Hole Size mm	11 mm
Dimension - L Length Overall mm	126 mm
Dimension - Length Overall inch	4.97 in
Dimension - N inch	0.50 in
Dimension - Outside Diameter inch	1.38 in

Dimension - Pad Width inch	2.01 in
Dimension - Strip Length inch	1-15/16
Dimension - Stud Size inch	3/8
Dimension - Z inch	0.52 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Size	800 kcmil
Conductor - Copper Str Size Range	800 kcmil
Conductor - Material	Copper

### Certifications and Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)