



YA4190

by Burndy
Catalog ID: YA4190

UNINSULATED COPPER COMPRESSION TERMINAL.

Product Details

General

Color Code	Gold
Connector Type	Terminal
Die Index	26
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated
UPC	781810367445
UPC 12 Digit	7818103674455

Dimensions

Dimension - B Length fraction	2-15/16 in
Dimension - B Length inch	2.94 in
Dimension - Bolt Hole Size inch	0.66 in
Dimension - Bolt Size fraction	5/8
Dimension - Height inch	4.49 in
Dimension - Hole Size inch	0.69 in
Dimension - Hole Size mm	18 mm
Dimension - L Length Overall mm	57 mm
Dimension - Length Overall inch	2.23 in
Dimension - N inch	0.66 in
Dimension - Outside Diameter inch	1.38 in
Dimension - Pad Width inch	2.01 in
Dimension - Strip Length inch	3
Dimension - Thread Size	5/8 in
Dimension - Z inch	0.67 in
Physical Attribute - Tongue Angle	90 Degree

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Size	850 kcmil
Conductor - Material	Copper

Certifications and Compliance

Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)