

YA42A5

by Burndy
Catalog ID: YA42A5

Prop 65 Notice

Al Tube Hylug, 2 Holes, 900 KCMIL Al, 1/2 IN Stud, 7.09 IN L, Gray, 303 Index.

UL Listed 90 DEG C, 600 V - 35 KV, Tongue Angle: Straight



Product Details

General

Application	For Aluminum & Copper Conductors
Color Code	Gray
Connector Type	Terminal
Die Index	303
Feature - Barrel Type	Standard
Material	Aluminum
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	TERMINALS, HYLUG
Temperature Rating	194
Trade Name	HYLUG™
Type	YA-A
UPC	781810637166
UPC 12 Digit	7818106371666

Dimensions

Dimension - D inch	3.13 in
Dimension - L Length Overall mm	180 mm
Dimension - Length Overall inch	7.09 in
Dimension - N inch	0.63 in
Dimension - Pad Width inch	1.62 in
Dimension - Strip Length inch	2 7/8
Dimension - Stud Size inch	1/2
Dimension - Z inch	0.77 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600

Voltage - Maximum	35000
-------------------	-------

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	3
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)