

YA442NDTSSV

by Burndy
Catalog ID: YA442NDTSSV

Prop 65 Notice

Copper Terminal, Silver Plated Finish, For 1000 KCMIL Code, NEMA Stud and Spacing, Solder Sealed Barrel Transition



Product Details

General

Application	Code Conductor Terminal
Color Code	White
Connector Type	Terminal
Die Index	27
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Insulation	N
Material	Copper
Plated	Y
Plating Type	Silver
Temperature Rating	194
Trade Name	HYLUG
Type	Standard Barrel, Silver Plated
UPC	781810525845
UPC 12 Digit	7818105258455

Dimensions

Diameter - Bolt	.56
Dimension - Hole Size mm	0 mm
Dimension - L Length Overall mm	0 mm
Dimension - Thread Size	-
Height	2.19 in
Length	7.14 in
Physical Attribute - Tongue Angle	Straight
Width	.33 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Size	1000 Kcmil
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	N
Certification - cULus	N
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	500
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)