



YA442TC38

by Burndy
Catalog ID: YA442TC38

Prop 65 Notice

Cu Tubing Compression Terminal, 2 Holes W/o Insp window, 1000 kcmil, 3/8" Stud, 1.00" Spacing, Long Brll

Product Details

General

Color Code	White
Connector Type	Terminal
Die Index	27
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated
UPC	781810080276
UPC 12 Digit	7818100802766

Dimensions

Dimension - B Length fraction	3 in
Dimension - B Length inch	3.00 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8 in
Dimension - D inch	2.03 in
Dimension - Hole Size inch	0.40 in
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	156 mm
Dimension - Length Overall inch	6.14 in
Dimension - N inch	0.50 in
Dimension - Outside Diameter inch	1.50 in
Dimension - Pad Width inch	2.19 in
Dimension - Strip Length inch	3-1/16 in
Dimension - Stud Size inch	3/8 in

Dimension - Z inch	0.53 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Size	1000 kcmil
Conductor - Copper Str Size Range	1000 kcmil
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	3
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)