

YA44L2TC12

by Burndy
Catalog ID: YA44L2TC12

Prop 65 Notice

COPPER COMPRESSION TERMINAL.



Product Details

General

Color Code	White
Connector Type	Terminal
Die Index	27
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Straight
Plated	Y
Plating Type	Tin -Plated
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810021163
UPC 12 Digit	7818100211633

Dimensions

Dimension - B Length inch	1.65 in
Dimension - Bolt Hole Size inch	1/2 in
Dimension - Bolt Size fraction	1/2
Dimension - Hole Size inch	0.52 in
Dimension - Hole Size mm	13 mm
Dimension - L Length Overall mm	128 mm
Dimension - Length Overall inch	5.05 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	1.5 in
Dimension - Pad Width inch	2.19 in
Dimension - Strip Length inch	1-15/16
Dimension - Stud Size inch	1/2 in
Dimension - Thread Size	1/2
Dimension - Z inch	0.55 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Solid Size	1000 kcmil
Conductor - Copper Str Size	1000 kcmil
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	3
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)