

# YA44L2TC38FX45

by Burndy  
Catalog ID: YA44L2TC38FX45

Prop 65 Notice

Cu Comp Terminal Flex Cond, Bvl Entry, 2 Hole/W/InspWindow, 777.7 kcmil(1925/#24)DLO, 750 kcmil FLEX, 600 V-35 kV, 3/8" Stud, 1.00" Spacing, 45° Bent, Std bbl



## Product Details

### General

Color Code	Yellow
Connector Type	Terminal
Die Index	L115
Feature - Barrel Style	<ul style="list-style-type: none"> <li>• Chamfered</li> <li>• Skived</li> </ul>
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Straight
Plated	Y
Plating Type	Tin -Plated
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810037522
UPC 12 Digit	7818100375222

### Dimensions

Dimension - B Length inch	1.65 in
Dimension - Bolt Hole Size inch	3/8 in
Dimension - Bolt Size fraction	3/8
Dimension - Height inch	3.07 in
Dimension - Hole Size inch	0.40 in
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	120 mm
Dimension - Length Overall inch	4.71 in
Dimension - N inch	0.50 in
Dimension - Outside Diameter inch	1.5 in
Dimension - Pad Width inch	2.19 in
Dimension - Strip Length inch	1-5/8 in
Dimension - Stud Size inch	3/8 in

Dimension - Thread Size	3/8
Dimension - Z inch	0.53 in
Physical Attribute - Tongue Angle	45 Degree

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper DLO Size	777.7 (1925/#24)
Conductor - Copper DLO Size Range	777.7 kcmil(1925/24)
Conductor - Copper Flex G Size	750
Conductor - Copper Flex G Size Range	750 kcmil/FLEX
Conductor - Copper Flex H Size	750
Conductor - Copper Flex I Size	750
Conductor - Copper Flex K Size	750
Conductor - Copper Flex M Size	750
Conductor - Copper Solid Size	750 kcmil/FLEX
Conductor - Copper Str Size	750 kcmil/FLEX
Conductor - Material	Copper

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity	10
-----------------------	----

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)