



YA44L2TC58FX

by Burndy
Catalog ID: YA44L2TC58FX

Prop 65 Notice

Copper Tubing Compression Terminal, 2 Holes W/insp Window, 777.7 (1925/#24) DLO, 5.52 IN L, 3.07 IN W, L115 Index, 5/8 IN Bolt

Product Details

General

Color Code	Yellow
Connector Type	Terminal
Die Index	L115
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Straight
Plated	Y
Plating Type	Tin -Plated
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810021088
UPC 12 Digit	7818100210888

Dimensions

Dimension - B Length inch	1.65 in
Dimension - Bolt Hole Size inch	5/8 in
Dimension - Bolt Size fraction	5/8
Dimension - Hole Size inch	0.69 in
Dimension - Hole Size mm	17 mm
Dimension - L Length Overall mm	141 mm
Dimension - Length Overall inch	5.55 in
Dimension - N inch	0.66 in
Dimension - Outside Diameter inch	1.5 in
Dimension - Pad Width inch	2.19 in
Dimension - Strip Length inch	1-5/8 in
Dimension - Stud Size inch	5/8 in
Dimension - Thread Size	5/8 in

Dimension - Z inch	0.68 in
--------------------	---------

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	777.7 (1925/#24)
Conductor - Copper DLO Size Range	777.7 kcmil(1925/24)
Conductor - Copper Flex G Size	750
Conductor - Copper Flex G Size Range	750 kcmil/FLEX
Conductor - Copper Flex H Size	750
Conductor - Copper Flex I Size	750
Conductor - Copper Flex K Size	750
Conductor - Copper Flex M Size	750
Conductor - Copper Solid Size	750 kcmil/FLEX
Conductor - Copper Str Size	750 kcmil/FLEX
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	20
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)