

YA44LNT38FX

by Burndy
Catalog ID: YA44LNT38FX

Prop 65 Notice

Cu compression narrow Tongue std barrel-Code conductor, Single hole/W/ insp window, 777.7 kcmil.1925/24.750 flex, 600V-35Kv, 3/8" stud, Yellow, L115 index



Product Details

General

Color Code	Yellow
Connector Type	Terminal
Die Index	L115
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
UPC	781810498255

Dimensions

Dimension - B Length fraction	1-11/16 in
Dimension - B Length inch	1.65 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - D inch	1.20 in
Dimension - L Length Overall mm	96 mm
Dimension - Length Overall inch	3.79 in
Dimension - N inch	0.53 in
Dimension - Outside Diameter inch	1.50 in
Dimension - Pad Width inch	1.50 in
Dimension - Strip Length inch	1-5/8
Dimension - Stud Size inch	3/8
Dimension - Z inch	0.67 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600

Voltage - Maximum	35000
-------------------	-------

Conductor Related

Conductor - Copper DLO Size	777.7 (1925/#24)
Conductor - Copper DLO Size Range	777.7 (1925/#24)
Conductor - Copper Flex G Size	750
Conductor - Copper Flex G Size Range	750
Conductor - Copper Flex H Size	750
Conductor - Copper Flex H Size Range	750
Conductor - Copper Flex I Size	750
Conductor - Copper Flex I Size Range	750
Conductor - Copper Flex K Size	750
Conductor - Copper Flex K Size Range	750
Conductor - Copper Flex M Size	750

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)