



YA44LTC38FX

by Burndy
Catalog ID: YA44LTC38FX

Prop 65 Notice

HYLUG FLEX 3/8IN BOLT

Product Details

General

| | |
|------------------------|-----------------------------|
| Connector Type | Terminal |
| Feature - Barrel Style | Chamfered |
| Feature - Barrel Type | Standard |
| Material | Copper |
| Plated | Y |
| Plating Type | Tin |
| Trade Name | HYLUG™ |
| Type | Standard Barrel, Tin Plated |
| UPC | 781810450109 |
| UPC 12 Digit | 7818104501099 |

Dimensions

| | |
|-----------------------------------|----------|
| Physical Attribute - Tongue Angle | Straight |
|-----------------------------------|----------|

Electrical Ratings

| | |
|--------------------------|-------|
| Rating - KVA | 35 kV |
| Rating - Minimum Voltage | 600 |
| Voltage - Maximum | 35000 |

Conductor Related

| | |
|----------------------|--------|
| Conductor - Material | Copper |
|----------------------|--------|

Certifications and Compliance

| | |
|------------------------------------|-----|
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)