

YA453T3W

by Burndy
Catalog ID: YA453T3W

Cu Tubing Compression Terminal, 1 Hole W/O InspWindow, 1300 Kcmil, 5/8" Stud, Uninsulated, Long



Product Details

General

Color Code	Orange
Connector Type	Terminal
Die Index	30
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	straight
Plated	Y
Plating Type	Hot - Tin plated
Trade Name	HYLUG™
Type	Long Barrel, Hot-Tin Plated
UPC	781810184004
UPC 12 Digit	7818101840044

Dimensions

Dimension - B Length inch	3.19 in
Dimension - Bolt Hole Size inch	0.69 in
Dimension - Bolt Size fraction	5/8
Dimension - Hole Size inch	0.69 in
Dimension - Hole Size mm	17 mm
Dimension - Inside Diameter inch	1.35 in
Dimension - L Length Overall mm	160 mm
Dimension - Length Overall inch	6.29 in
Dimension - N inch	0.94 in
Dimension - Outside Diameter inch	1.74 in
Dimension - Pad Width inch	2.47 in
Dimension - Strip Length inch	2-1/16 in
Dimension - Stud Size inch	5/8 in
Dimension - Thread Size	5/8 in
Dimension - Z inch	0.94 in

Physical Attribute - Tongue Angle	Straight
-----------------------------------	----------

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Solid Size	1300 Kcmil
Conductor - Copper Str Navy Size	1300 (127) Navy
Conductor - Copper Str Navy Size Range	1300 (127) Navy
Conductor - Copper Str Size	1300 Kcmil
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	10
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)