



YA454N

by Burndy
Catalog ID: YA454N

Prop 65 Notice

Copper Compression Lug, 4 Hole w/o Inspection Window, 1250 kcmil, 1/2" Stud, 1-3/4" Stud Hole Spacing, Long Barrel, Tin Plated.

Features: 45 DEG And 90 DEG Angles Are Available, Tongue Angle: Straight, Tools, Die Set Catalog Number, And (number Of Crimps): Hydraulic: Y46 Tool, P45RT Die, Color Code: Yellow, Wire Strip Length: 3-1/4 IN, Die Index: 29

Product Details

General

Application	For use on copper compression connections
Color Code	Yellow
Connector Type	Terminal
Die Index	29
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	4
Physical Attribute - Tongue Type	straight
Plated	Y
Plating Type	Tin plated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated
UPC	781810035665
UPC 12 Digit	7818100356655

Dimensions

Dimension - B Length inch	3.19 in
Dimension - Bolt Size fraction	1/2
Dimension - F Width Center to Center inch	1.75 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	189 mm
Dimension - Length Overall inch	7.44 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	1.69 in
Dimension - Pad Width inch	3 in
Dimension - Strip Length inch	3-1/4 in

Dimension - Stud Size inch	1/2 in
Dimension - Thread Size	1/2
Dimension - Z inch	0.64 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Solid Size	1250 Kcmil
Conductor - Copper Str Size	1250 Kcmil
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)