

YA45L12

by Burndy
Catalog ID: YA45L12

Prop 65 Notice

Cu Tubing Compression Terminal, 1 Hole W/ InspWindow, 1250 Kcmil, 1/2" Stud, Uninsulated, Long



Product Details

General

Color Code	Yellow
Connector Type	Terminal
Die Index	29
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	straight
Plated	Y
Plating Type	Tin plated
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810349038
UPC 12 Digit	7818103490388

Dimensions

Dimension - B Length inch	2 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - Bolt Size fraction	1/2
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	113 mm
Dimension - Length Overall inch	4.43 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	1.69 in
Dimension - Pad Width inch	2.46 in
Dimension - Strip Length inch	2-1/6 in
Dimension - Stud Size inch	1/2 in
Dimension - Thread Size	1/2
Dimension - Z inch	0.64 in

Physical Attribute - Tongue Angle	Straight
-----------------------------------	----------

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Solid Size	1250 Kcmil
Conductor - Copper Str Size	1250 Kcmil
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	10
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)