

# YA462NU

by Burndy  
Catalog ID: YA462NU

Prop 65 Notice

Copper Compression Lug, Blank Tongue, w/o Inspection Window, 1500 kcmil, 3/8" Min Stud, Short Barrel, Tin Plated



## Product Details

### General

Color Code	Green
Connector Type	Terminal
Die Index	31
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	0
Plated	Y
Plating Type	Tin plated
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated
UPC	781810524909
UPC 12 Digit	7818105249099

### Dimensions

Dimension - B Length inch	3.19 in
Dimension - L Length Overall mm	192 mm
Dimension - Length Overall inch	7.55 in
Dimension - Outside Diameter inch	1.84 in
Dimension - Pad Width inch	2.69 in
Dimension - Strip Length inch	3-1/4
Dimension - Stud Size inch	3/8
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper Str Size	1500 kcmil
Conductor - Material	Copper

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	3
-----------------------	---

**For further technical assistance, please contact us**

### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)