

YA46LB

by Burndy
Catalog ID: YA46LB

One hole Standard barrel Cu Compression Terminal with Belled End ,
1500 Kcmil, 3/4" stud, Tin plated



Product Details

General

Color Code	Green
Connector Type	Terminal
Die Index	31
Feature - Barrel Style	Belled
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin plated
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated
UPC	781810021262
UPC 12 Digit	7818100212622

Dimensions

Dimension - B Length inch	2.00 in
Dimension - Bolt Hole Size inch	0.91 in
Dimension - Bolt Size fraction	3/4
Dimension - Hole Size inch	0.81 in
Dimension - Hole Size mm	21 mm
Dimension - L Length Overall mm	140 mm
Dimension - Length Overall inch	5.50 in
Dimension - N inch	1.12 in
Dimension - Outside Diameter inch	1.84 in
Dimension - Pad Width inch	2.69 in
Dimension - Strip Length inch	2-1/16
Dimension - Thread Size	3/4 in
Dimension - Z inch	1.13 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	1111.1 (2750/#24)
Conductor - Copper Str Size	1500 kcmil
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	10
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)