

YA472NU

by Burndy
Catalog ID: YA472NU

Prop 65 Notice

Cu Tubing Compression Terminal, W/ InspWindow, 1750 Kcmil, Undrilled, Uninsulated, Long barrel



Product Details

General

Color Code	Gray
Connector Type	Terminal
Die Index	33
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	0
Plated	Y
Plating Type	Tin plated
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated
UPC	781810020883
UPC 12 Digit	7818100208833

Dimensions

Dimension - B Length inch	3.44 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - L Length Overall mm	200 mm
Dimension - Length Overall inch	7.89 in
Dimension - Outside Diameter inch	1.98 in
Dimension - Pad Width inch	2.90 in
Dimension - Strip Length inch	3-1/2
Dimension - Stud Size inch	3/8
Dimension - Thread Size	1/2
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Size	1750 kcmil
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)