

YA47

by Burndy
Catalog ID: YA47

Prop 65 Notice

Cu Tubing Compression Terminal, 1 Hole W/O InspWindow, 1750 Kcmil, 3/4" Stud, Uninsulated, Long barrel flex conductor



Product Details

General

Color Code	Brown
Connector Type	Terminal
Die Index	34
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	straight
Plated	Y
Plating Type	Electro-Tin plated
Trade Name	HYLUG™
Type	Long Barrel, Electro-Tin Plated
UPC	781810316986
UPC 12 Digit	7818103169866

Dimensions

Dimension - B Length inch	3.44 in
Dimension - Bolt Hole Size inch	0.81 in
Dimension - Bolt Size fraction	3/4
Dimension - Hole Size inch	0.81 in
Dimension - Hole Size mm	21 mm
Dimension - L Length Overall mm	162 mm
Dimension - Length Overall inch	6.38 in
Dimension - N inch	0.75 in
Dimension - Outside Diameter inch	1.98 in
Dimension - Pad Width inch	2.90 in
Dimension - Strip Length inch	3-1/2 in
Dimension - Stud Size inch	3/4 in
Dimension - Thread Size	3/4 in
Dimension - Z inch	0.77 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Solid Size	1750 Kcmil
Conductor - Copper Str Size	1750 Kcmil
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	3
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)