



YA482NFXB

by Burndy
Catalog ID: YA482NFXB

Copper Compression Lug, 2 Hole w/o Inspection Window, 1550 kcmil, 1/2" Stud, long Barrel, Tin - Electro Plated.

Product Details

General

Color Code	Brown
Connector Type	Terminal
Die Index	33
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Straight
Plated	Y
Plating Type	Electro-Tin
Temperature Rating	194
Trade Name	HYLUG™
Type	Long barrel, Tin-Plated
UPC	781810282250
UPC 12 Digit	7818102822500

Dimensions

Dimension - B Length fraction	3-7/8 in
Dimension - B Length inch	3.9 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - Bolt Size fraction	1/2
Dimension - D inch	3.01 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	214 mm
Dimension - Length Overall inch	8.42 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	2.13 in
Dimension - Pad Width inch	3.1 in
Dimension - Strip Length inch	4-1/16 in
Dimension - Stud Size inch	1/2 in

Dimension - Thread Size	1/2
Dimension - Z inch	0.64 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Flex K Size	1550
Conductor - Copper Str Size	1550 kcmil
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	5
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)