



YA482N

by Burndy
Catalog ID: YA482N

Prop 65 Notice

Copper Two Hole HYLUG - Long Barrel ,Straight Pad for 200 kcmil,1/2" Bolt Hole with 1-3/4" Spacing,Tin Plated,Color: Brown,Die Index: 34.

Features: UL Listed 90 DEG C, 600 V - 35 KV, 45 DEG And 90 DEG Angles Are Available, Temperature Rating: 90 DEG C, Finish: Electro-Tin Plated, Wire Strip Length: 3-1/2 IN, Tongue Angle: Straight, Color Code: Brown, Conductor Type: Commercial Stranded Copper, Die Index: 34, Dieless Tools (number Of Crimps): Y644HS Tool, (1), Y81KFT, Y81KFTMBH, PAT81KFT-18V Tool, (4)

Product Details

General

Application	For use on copper compression connections
Color Code	Brown
Connector Type	Terminal
Die Index	34
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Straight
Plated	Y
Plating Type	Electro-Tin
Sub Brand	HYLUG
Temperature Rating	194
Trade Name	HYLUG™
Type	Long barrel, Tin-Plated
UPC	781810525517
UPC 12 Digit	7818105255177

Dimensions

Dimension - B Length fraction	3-7/16 in
Dimension - B Length inch	3.44 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - Bolt Size fraction	1/2
Dimension - D inch	3.02 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	203 mm
Dimension - Length Overall inch	7.98 in

Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	2.13 in
Dimension - Pad Width inch	3.1 in
Dimension - Strip Length inch	3-1/2 in
Dimension - Stud Size inch	1/2 in
Dimension - Thread Size	1/2
Dimension - Z inch	0.64 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Size	2000 kcmil
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	3
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)