



YA4864N

by Burndy
Catalog ID: YA4864N

Prop 65 Notice

BURNDY; HYLUG; YA; Features: Four Hole Copper compression, Long Barrel; For use on copper compression connections; RoHS Compatible

Product Details

General

Connector Type	Terminal
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	4
Plated	Y
Plating Type	Tin
Temperature Rating	194
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated
UPC	781810080245
UPC 12 Digit	7818100802455

Dimensions

Dimension - B Length fraction	4-11/16 in
Dimension - B Length inch	4.69 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - D inch	3.02 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	238 mm
Dimension - Length Overall inch	9.38 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	2.38 in
Dimension - Pad Width inch	3.46 in
Dimension - Strip Length inch	4-3/4
Dimension - Stud Size inch	1/2
Dimension - Thread Size	1/2
Dimension - Z inch	0.64 in

Length	9.38 in
Outside Diameter	2.38 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Size	2500 kcmil
Conductor - Copper Str Size Range	2500 kcmil
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	3
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)