

YA4C2L3

by Burndy
Catalog ID: YA4C2L3

Prop 65 Notice

Copper Tubing Terminal, 2 Holes /W/ insp Window, #4 CLASS B, C AWG, 40 Navy, 5/6 IN Bolt, 8, 346 Index, Gray, Electro Tin Plated.



Product Details

General

| | |
|--------------------------------------|---------------------------------------------------------------------------------|
| Color Code | Gray |
| Connector Type | Terminal |
| Die Index | 8 |
| Feature - Barrel Style | <ul style="list-style-type: none"> • Chamfered • Skived |
| Feature - Barrel Type | Standard |
| Material | Copper |
| Physical Attribute - Number of Holes | 2 |
| Plated | Y |
| Plating Type | Tin - Electro Plated |
| Trade Name | HYLUG™ |
| Type | Standard Barrel, Tin Plated |
| UPC | 781810018101 |

Dimensions

| | |
|-----------------------------------|----------|
| Dimension - B Length fraction | 13/16 in |
| Dimension - B Length inch | 0.81 in |
| Dimension - D inch | 1.59 in |
| Dimension - Hole Size mm | 8 mm |
| Dimension - Inside Diameter inch | 0.25 in |
| Dimension - L Length Overall mm | 69 mm |
| Dimension - Length Overall inch | 2.70 in |
| Dimension - N inch | 0.34 in |
| Dimension - Outside Diameter inch | 0.34 in |
| Dimension - Pad Width inch | 0.56 in |
| Dimension - Z inch | 0.37 in |
| Physical Attribute - Tongue Angle | Straight |

Electrical Ratings

| | |
|--------------------------|-------|
| Rating - KVA | 35 kV |
| Rating - Minimum Voltage | 600 |
| Voltage - Maximum | 35000 |

Conductor Related

| | |
|----------------------------------------|--------------|
| Conductor - Copper DLO Size Range | N/A |
| Conductor - Copper Str Navy Size | 40 (19) Navy |
| Conductor - Copper Str Navy Size Range | 40 (19) Navy |
| Conductor - Copper Str Size | 4 AWG |
| Conductor - Copper Str Size Range | 4 AWG |
| Conductor - Material | Copper |

Certifications and Compliance

| | |
|------------------------------------|-----|
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|----|
| Minimum Pack Quantity | 50 |
|-----------------------|----|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)