

YA4CG8

by Burndy
Catalog ID: YA4CG8

Cu Compression Skived Back Terminal, 1 Hole, #5 (91/#24)DLO, 5/16" Stud



Product Details

General

Connector Type	Terminal
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin
Temperature Rating	194
UPC	781810130759
UPC 12 Digit	7818101307599

Dimensions

Dimension - B Length fraction	1/2 in
Dimension - B Length inch	0.50 in
Dimension - Bolt Hole Size inch	0.33 in
Dimension - D inch	0.75 in
Dimension - Hole Size inch	0.34 in
Dimension - Hole Size mm	9 mm
Dimension - L Length Overall mm	37 mm
Dimension - Length Overall inch	1.44 in
Dimension - N inch	0.31 in
Dimension - Outside Diameter inch	0.34 in
Dimension - Pad Width inch	0.58 in
Dimension - Z inch	0.44 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	5 (91/#24) DLO
Conductor - Copper DLO Size Range	5 (91/#24) DLO
Conductor - Copper Str Size	5 AWG
Conductor - Copper Str Size Range	5 AWG
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	500
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)