

YA4CL2TC1445

by Burndy
Catalog ID: YA4CL2TC1445

Prop 65 Notice

Cu compression tubular terminals-code conductor, 2 holes/W/O/ insp window, #4 AWG, Tin plated, Grey, 8 or 346 index.

Features: Compression Terminal, With Inspection Window, Die Index: 8 or 346, Strip Length: 7/8 IN, Tongue Angle: 45 DEG, Finish: Electro-Tin Plated



Product Details

General

Application	For Use On: UL Listed 90 DEG C, 600 Volts to 35kV, Code Conductor
Color Code	Gray
Connector Type	Terminal
Die Index	8 ; 346
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin Plating
Sub Brand	TERMINALS, HYLUG
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810317341
UPC 12 Digit	7818103173411

Dimensions

Dimension - B Length fraction	13/16 in
Dimension - B Length inch	0.81 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Height inch	1.02 in
Dimension - Hole Size inch	0.27 in
Dimension - Hole Size mm	7 mm
Dimension - L Length Overall mm	56 mm
Dimension - Length Overall inch	2.2 in
Dimension - N inch	0.25 in
Dimension - Outside Diameter inch	0.34 in
Dimension - Pad Width inch	0.5 in
Dimension - Strip Length inch	7/8 in

Dimension - Stud Size inch	1/4
Dimension - Z inch	0.68
Physical Attribute - Tongue Angle	45 Degree

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Solid Size	#4 AWG
Conductor - Copper Str Navy Size	40 (19) Navy
Conductor - Copper Str Navy Size Range	40 (19) Navy
Conductor - Copper Str Size	#4 AWG
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)