

# YA4CT7DTS

by Burndy  
Catalog ID: YA4CT7DTS

Cu Tubing Compression Terminal, Sealed, 1 Hole, #4 Str. Commercial Cu Cable, 3/8" Stud



## Product Details

### General

Color Code	Gray
Connector Type	Terminal
Die Index	8;346
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Straight
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated, Sealed
UPC	781810113745
UPC 12 Digit	7818101137455

### Dimensions

Dimension - B Length inch	1.12
Dimension - Bolt Hole Size inch	0.4
Dimension - Hole Size inch	0.4
Dimension - Hole Size mm	10
Dimension - L Length Overall mm	58
Dimension - Length Overall inch	2.27
Dimension - N inch	0.41
Dimension - Outside Diameter inch	0.34
Dimension - Pad Width inch	0.58
Dimension - Strip Length inch	1-3/16 in
Dimension - Stud Size inch	3/8 in
Dimension - Z inch	0.42
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper Solid Size	4 AWG
Conductor - Copper Str Size	4 AWG
Conductor - Material	Copper

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity	100
-----------------------	-----

### For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)