

YA4CTC3845

by Burndy
Catalog ID: YA4CTC3845

Prop 65 Notice

Cu Tubing HYLUG™ , 1 Hole, #4 Str. Stranded Cu Cable



Product Details

General

Color Code	Gray
Connector Type	Terminal
Die Index	8;346
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Straight
Plated	Y
Plating Type	Electro-Tin
Trade Name	HYLUG™
Type	Long Barrel, Electro-Tin Plated
UPC	781810309438
UPC 12 Digit	7818103094388

Dimensions

Dimension - B Length inch	1.12
Dimension - Bolt Hole Size inch	0.4
Dimension - Height inch	1.25 in
Dimension - Hole Size inch	0.4
Dimension - Hole Size mm	10
Dimension - L Length Overall mm	51
Dimension - Length Overall inch	2.02
Dimension - N inch	0.41
Dimension - Outside Diameter inch	0.34
Dimension - Pad Width inch	0.58
Dimension - Strip Length inch	1-3/16 in
Dimension - Stud Size inch	3/8 in
Dimension - Z inch	0.42
Physical Attribute - Tongue Angle	45 Degree

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Solid Size	4 AWG
Conductor - Copper Str Navy Size	40 (19) Navy
Conductor - Copper Str Navy Size Range	40 (19) Navy
Conductor - Copper Str Size	4 AWG
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	5
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)