



## YA5C2NU

by Burndy  
Catalog ID: YA5C2NU

Prop 65 Notice

BURNDY; HYLUG; YA-2NU; Features: Copper compression, Long Barrel, Blank tongue terminal; For use on copper compression connections; RoHS Compatible

## Product Details

### General

Color Code	Blue
Connector Type	Terminal
Die Index	7
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810513002
UPC 12 Digit	7818105130022

### Dimensions

Dimension - B Length inch	1.12 in
Dimension - L Length Overall mm	113 mm
Dimension - Length Overall inch	4.43 in
Dimension - Pad Width inch	0.83 in
Dimension - Strip Length inch	1-3/16
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Material	Copper

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No

Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	50
-----------------------	----

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)