

YA5CL4B

by Burndy
Catalog ID: YA5CL4B

Prop 65 Notice

COPPER COMPRESSION TERMINAL.



Product Details

General

Connector Type	Terminal
Feature - Barrel Style	<ul style="list-style-type: none"> Belled Skived
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	Standard Belled Barrel, Tin Plated
UPC	781810192283
UPC 12 Digit	7818101922833

Dimensions

Dimension - B Length fraction	13/16 in
Dimension - B Length inch	0.81 in
Dimension - D inch	0.83 in
Dimension - Hole Size inch	0.40 in
Dimension - Hole Size mm	10 mm
Dimension - Inside Diameter inch	0.23 in
Dimension - L Length Overall mm	49 mm
Dimension - Length Overall inch	1.92 in
Dimension - N inch	0.41 in
Dimension - Outside Diameter inch	0.30 in
Dimension - Pad Width inch	0.54 in
Dimension - Z inch	0.42 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
--------------	-------

Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Navy Size	30 (19) Navy
Conductor - Copper Str Navy Size Range	30 (19) Navy
Conductor - Copper Str Size	5 AWG
Conductor - Copper Str Size Range	5 AWG
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	10
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
 47 East Industrial Park Drive
 Manchester, New Hampshire 03109

Customer Service Hours:
 8 AM - 8 PM Eastern Monday-Friday
 Emergency Service 24-hours/365 Days
 Phone: 1-800-346-4175
 1-603-647-5299 (International)