

# YA5CLBLD

by Burndy  
Catalog ID: YA5CLBLD

Copper Belled HYLUG™, 1 Hole with Inspection Window, 5 STR copper cable



## Product Details

### General

Color Code	Blue
Connector Type	Terminal
Die Index	7;1014
Feature - Barrel Style	Belled
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Straight
Plated	Y
Plating Type	Lead
Trade Name	HYLUG™
Type	Standard Belled, Lead Plated
UPC	781810192290
UPC 12 Digit	7818101922900

### Dimensions

Dimension - B Length inch	0.81
Dimension - Bolt Hole Size inch	0.272
Dimension - Hole Size inch	0.272
Dimension - Hole Size mm	6.91
Dimension - L Length Overall mm	43.9
Dimension - Length Overall inch	1.173
Dimension - N inch	0.31
Dimension - Outside Diameter inch	0.3
Dimension - Pad Width inch	0.44
Dimension - Strip Length inch	7/8 in
Dimension - Stud Size inch	1/4 in
Dimension - Z inch	0.328
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper DLO Size	6 (61/#24) DLO
Conductor - Copper Flex G Size	6 AWG
Conductor - Copper Flex H Size	6 AWG
Conductor - Copper Flex I Size	6 AWG
Conductor - Copper Flex K Size	6 AWG
Conductor - Copper Flex M Size	6 AWG
Conductor - Copper Flex M Size Range	6 AWG
Conductor - Copper Solid Size	5 AWG
Conductor - Copper Str Navy Size	30 (19) Navy
Conductor - Copper Str Navy Size Range	30 (19) Navy
Conductor - Copper Str Size	5 AWG
Conductor - Material	Copper

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	NC
UL Listed	Yes

### Logistics

Minimum Pack Quantity	200
-----------------------	-----

### For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)