

YA6C2NT8

by Burndy
Catalog ID: YA6C2NT8

Prop 65 Notice

Copper HYLUG™, Narrow, 2 holes W/O insp window, #6 Str #6 Sol, #8 stud, 7 or 374 index, Blue, Tin Plated



Product Details

General

Color Code	Blue
Connector Type	Terminal
Die Index	7;374
Feature - Barrel Style	Chamfered
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
UPC	781810672495

Dimensions

Dimension - B Length fraction	1-1/8 in
Dimension - B Length inch	1.12 in
Dimension - Bolt Hole Size inch	0.18 in
Dimension - L Length Overall mm	63 mm
Dimension - Length Overall inch	2.47 in
Dimension - Outside Diameter inch	0.29 in
Dimension - Pad Width inch	0.33 in
Dimension - Strip Length inch	1-3/16 in
Dimension - Stud Size inch	#8
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Solid Size	6 AWG
Conductor - Copper Solid Size Range	6 AWG

Conductor - Copper Str Size	6 AWG
Conductor - Copper Str Size Range	6 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Str-Size• CU C Solid-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)