



YA6CL190

by Burndy
Catalog ID: YA6CL190

Prop 65 Notice

Copper HYLUG™, Short Barrel, Single hole /W/ insp window, #6 Str #6 Sol, #8 #10 stud, 7 or 374 index, Blue, Electro-Tin Plated, 90 Degree Bend

Product Details

General

Color Code	Blue
Connector Type	Terminal
Die Index	7;374
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810085479

Dimensions

Dimension - B Length fraction	9/16 in
Dimension - B Length inch	0.54 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - D inch	0.49 in
Dimension - Height inch	0.94 in
Dimension - Hole Size mm	5 mm
Dimension - L Length Overall mm	18 mm
Dimension - Length Overall inch	0.72 in
Dimension - N inch	0.22 in
Dimension - Outside Diameter inch	0.29 in
Dimension - Pad Width inch	0.42 in
Dimension - Strip Length inch	9/16
Dimension - Stud Size inch	#10;#8
Dimension - Z inch	0.27 in
Physical Attribute - Tongue Angle	90 Degree

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Size	6 AWG
Conductor - Copper Str Size Range	6 AWG
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)