



YA6CLNT6U

by Burndy
Catalog ID: YA6CLNT6U

Prop 65 Notice

Cu Terminal, 1 Hole/W/insp W, #6STR(.184), 6" stud, Tin plated, Blue, 6 Index

Product Details

General

Color Code	Blue
Connector Type	Terminal
Die Index	7
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	0
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
UPC	781810354032

Dimensions

Dimension - B Length fraction	9/16 in
Dimension - B Length inch	0.54 in
Dimension - D inch	0.44 in
Dimension - L Length Overall mm	30 mm
Dimension - Length Overall inch	1.17 in
Dimension - Outside Diameter inch	0.29 in
Dimension - Pad Width inch	0.29 in
Dimension - Strip Length inch	7/8
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
-----------------------------------	-----

Conductor - Copper Solid Size	6 AWG
Conductor - Copper Solid Size Range	6 AWG
Conductor - Copper Str Size	6 AWG
Conductor - Copper Str Size Range	6 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)