



## YA8C2LN

by Burndy  
Catalog ID: YA8C2LN

Prop 65 Notice

Cu Comp Terminal Code Cond, Bvl Entry, 2 Hole/W/InspWindow, #8 AWG Str Code, 23 Navy, 600 V-35 kV, 1/2" Stud, 1.75" Spacing, Std bbl, Red, 49 Index.

Features: UL Listed 90 DEG C, 600 V - 35 KV, 45 DEG And 90 DEG Angles Are Available

## Product Details

### General

Application	For Code Conductor
Color Code	Red
Connector Type	Terminal
Die Index	49
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	TERMINALS, HYLUG
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810044612

### Dimensions

Dimension - B Length fraction	7/16 in
Dimension - B Length inch	0.44 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - D inch	1.26 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	95 mm
Dimension - Length Overall inch	3.75 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	0.27 in
Dimension - Pad Width inch	0.83 in
Dimension - Strip Length inch	7/16
Dimension - Stud Size inch	1/2
Dimension - Z inch	0.64 in
Physical Attribute - Tongue Angle	Straight

## Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

## Conductor Related

Conductor - Copper Str Navy Size	23 (7) Navy
Conductor - Copper Str Navy Size Range	23 (7) Navy
Conductor - Copper Str Size	8 AWG
Conductor - Copper Str Size Range	8 AWG
Conductor - Material	Copper

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)