

YA8C2NT8

by Burndy
Catalog ID: YA8C2NT8

Prop 65 Notice

Copper HYLUG™, 2 Holes W/O InspWindow, #8 AWG Str Code, 23 Navy, 600 V-35 kV, #8 Stud, Red, 49 Index, Tin plated



Product Details

General

Color Code	Red
Connector Type	Terminal
Die Index	49
Feature - Barrel Style	Chamfered
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
UPC	781810672488

Dimensions

Dimension - B Length inch	0.81 in
Dimension - Bolt Hole Size inch	0.18 in
Dimension - L Length Overall mm	54 mm
Dimension - Length Overall inch	2.14 in
Dimension - Outside Diameter inch	0.27 in
Dimension - Pad Width inch	0.33 in
Dimension - Strip Length inch	7/8 in
Dimension - Stud Size inch	#8
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Navy Size	23 (7) Navy
Conductor - Copper Str Navy Size Range	23 (7) Navy
Conductor - Copper Str Size	8 AWG

Conductor - Copper Str Size Range	8 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Str-Size• CU C Str Navy-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)